



Key Features

Custom lengths



Nylon construction



Good chemical resistance



Discrete



Compatible with VESDA, VESDA-E, ICAM, FAAST, Airsense and Securiton



Overview

Capillary pipe is used to drop down to 10mm sampling points. The maximum recommended length is 8m per drop and all capillary pipes must have an equal length to avoid air flow issues.

Tech Specs

Material	Nylon
External Diameter	10mm
Length	100m
Burst Pressure	995 PSI / 68 bar
Weight	4.47kg

Ordering Information

Part Number	Description
22-075	Natural 10mm Capillary Pipe 100m Drum