



## Key Features

|   |   |
|---|---|
| Custom lengths  | ✔ |
| Nylon construction  | ✔ |
| Good chemical resistance  | ✔ |
| Discrete  | ✔ |
| Compatible with VESDA, VESDA-E, ICAM, FAAST, Airsense and Securiton | ✔ |

## Overview

Capillary pipe is used to drop down to 10mm sampling points. The maximum recommended length is 8m per drop and all capillary pipes must have an equal length to avoid air flow issues.

## Tech Specs

|                   |                  |
|-------------------|------------------|
| Material          | Nylon            |
| External Diameter | 10mm             |
| Length            | 100m             |
| Burst Pressure    | 995 PSI / 68 bar |
| Weight            | 4.47kg           |

## Ordering Information

| Part Number | Description                       |
|-------------|-----------------------------------|
| 22-074      | Red 10mm Capillary Pipe 100m Drum |